

# eFLASHER VIII

Light and convenient, the *eFLASHER VIII* is ideal for every deaf computer and videoconference user. *eFLASHER VIII* provides one (1) flash for each regular (TTY) telephone ring, double-flashes (2) for each Broadband ring, and computer flashes three times for a distinguished noticeable flashing signal lamp. Whether you are away from your T.V. or telephone and cannot hear the ringing sound, the *eFLASHER VIII* is designed to quickly alert users to any incoming e-mails, TTY-PC, instant message (IM), IP-VRS, VRS, or videochat signal calls, plus regular calls for TTY. The *eFLASHER VIII* works with D-Link (DVC-1000), Sorensen (VP-100), or any other similar products that have the cadence ringing output port jack available. The *eFLASHER VIII* operates a built-in X-10 wireless transmitting system feature.

### **Prices:**

- \$139.95 per unit (#EFL800)
- \$8.50 shipping/handling
- Includes an "easy-to-read" instruction manual
- Compact lightweight size: (7.0" W x 5.0" D x 2.0" H)
- Meets FCC & U.L.
- One year warranty
- Quantities over 10 units are available at discounted price
- See reverse page for eFLASHER VIII simplify installation

# **Order:**

 Charge cards (Discover/ MC/VISA), Qualifying Purchase Order, Check, Money Order to:

#### **DEAFWORKS**

P.O. Box 1265 Provo, UT 84603-1265

TTY: (801) 465-1957 FAX: (801) 465-1958 eflasher@deafworks.com www.deafworks.com

## Basic eFLASHER VIII Installation Phone Jack 03 0 **Broadband** ("Y" Jack) 0 Jack **Broadband** Videophone\* (Any TTYs) PC/MAC III $\Box$ Soft/Norm Lamp outlet **OPTIONAL** flash switch Telephone Telephone (Jack1) (Jack2) Audio jacks eFLASHER VIII O 000 000 Lamp Plug-in SPKR SPKR (up to 100 W) (Right) (Left) Feature FLASH switch: SOFT (slow) or NORM (reg) (wireless) NOTE: Unlimited NOTE: eFLASHER VIII provides one (1) ∥'დ numbers of X-10 flash for each telephone ring, double-Lamp Modules to flashes (2) for each Broadband ring, and cover all rooms. three flashes (3) for each computer call. For computer call, a sound .WAV file must be used to operate which it can be The DEAFWORKS Co. download from manufacturer's website: P.O. Box 1265 http://www.deafworks.com/eFLASHER/download.html Provo, UT 84603-1265 \* D-Link (DVC-1000), Sorenson (VP-100), TTY: (801) 465-1957 or any other similar products that have FAX: (801) 465-1958 the candence ringing output port jack eflasher@deafworks.com available to eFLASHER's unit input jack.